


Ecotron Anyview Series

Mobile C-Arm System

Excellent radiographic imaging at an economical price

The Anyview 500R Surgical Mobile C-Arm combines innovation and ease of use, making it the ideal option for a variety of applications.



SPECIFICATIONS

System Power Requirement

- ✓ Line Voltage: 100~120V 50 / 60Hz
- ✓ Line Phase: Single

X-ray Generator

- ✓ Type: HFG INVERTER
- ✓ Output Power: 2.8kW
- ✓ Fluoroscopy:
 - Continuous mode: 0.5~10mA
 - Pulsed mode: 0.5~20mA
 - Boosted mode: 30mA
 - ABC mode: YES
- ✓ Radiography mode:
 - kV range: 40~125kV
 - mA range: 20~40
 - mAs range: 0.8~200mAs

Image Intensifier

- ✓ Input field view size: 9"
- ✓ Nominal entrance field size: 9 / 6 / 4.5" or 12 / 9 / 6"
- ✓ Central resolution: 54 / 62 / 70 lp/cm
- ✓ Contrast ratio (10%): 36
- ✓ Cassette holder size: 10 x 12"

Digital Imaging System (DIS)

- ✓ Type: AIS
- ✓ Intel Core i3-2130 (3.4GHz)
- ✓ Windows 7 or higher
- ✓ PC Spec: 4GB DDR3 SDRAM, 1600MHz-1X4GB | 500GB or higher

1564-2017-08-04

Advanced X-ray Generator Technology

- ✓ Immediate video imaging with the touch of a button.
- ✓ Reduce radiation doses with pulse frequencies of 8, 15 or 30 Hz.

Intelligent Dose Reduction

Minimum dose and best quality

Establish Imaging Area

Kv and mA settings automatically optimize to the appropriate setting for each body part.

Select Intelligent Dose Reduction Mode

ABS Mode, Pulse Mode (8, 15, or 30), Activation.

Virtual Collimator

The collimator is positioned in the imaging area without using radiation.

Dose Reduction

Reduce pulse frequency and pulse width.

AnyView Intelligent Image Processing

Activated during automatic dose reduction mode.

Anyview Intelligent Image Processing Module

- ✓ Comprehensive video imaging provides unparalleled definition and clarity.
- ✓ Produces up to 30 frames per second in any imaging mode.

Built-in Patient Data Software

Easily store patient dose information and images with built-in, user-friendly DAP software.

SPECIFICATIONS

X-ray Tube

- ✓ X-ray tube type: Rotating
- ✓ Max kV: 125kV
- ✓ Focal spot: Small: 0.3mm | Large: 0.6mm
- ✓ Target angle: 10°
- ✓ Anode heat storage capacity: 150kJ

Collimator

- ✓ Type: Motorized
- ✓ Opening/Closing: 2 way
- ✓ Rotation: 360°
- ✓ Iris: Motorized

Camera

- ✓ Type: CCD
- ✓ Pixel size: 1K x 1K

Monitor

- ✓ Type: TFT - LCD DUAL
- ✓ Size: 19"
- ✓ Quantity: 2

Options

- ✓ Dose Area Meter
- ✓ Digital Imaging system with PACS